


DANAHER MOTION
 AKD DRIVE 1.5–6 AMP
 AKM MOTOR EURO STYLE
 POWER CABLE

NOTE: THIS ASSEMBLY IS RoHS COMPLIANT



FACE VIEW

WIRING DIAGRAM



VP-507BEAN-**
 Cable Jacket Material – TPE
 Outside Diameter – $\varnothing 9.40 \pm 0.25$ mm
 BEND RADIUS – 94.00mm
 Static flex Rating – Not Rated
 Dynamic Flex Rating – Not Rated
 Temperature Rating – 105C
 Voltage Rating – 600V
 Assembly Weight – *.****kg

VP-507BEAN-01	0.258KG
VP-507BEAN-03	0.536KG
VP-507BEAN-06	0.955KG
VP-507BEAN-09	1.372KG
VP-507BEAN-12	1.789KG

VP-507BEAN-xx

N/C DENOTES NO CONNECTION