



VF-RA2474N-01-0	0.273KG
VF-RA2474N-03-0	0.551KG
VF-RA2474N-06-0	0.968KG
VF-RA2474N-09-0	1.385KG
VF-RA2474N-12-0	1.793KG
ASSEMBLY WEIGHT	

VF-RA2474N-\*\*

- 1) Cable Specifications:  
 Jacket Material: TPE  
 Outside Diameter:  $\varnothing 9.65\text{mm} \pm 0.35\text{mm}$   
 Bend Radius (min): 96.5mm  
 Static Flex Rating: Not Rated  
 Dynamic Flex Rating: Not Rated  
 Temperature Rating: 105°C  
 Voltage Rating: 300V  
 AWM Style: UL20327
- 2) Assembly Weight – SEE TABLE
- 3) This assembly is RoHS COMPLIANT

= TWISTED PAIR

N/C DENOTES NO CONNECTION

CONNECTOR BACKSHELL SHIELDED 360° (BOTH ENDS)

DANAHER MOTION  
 S200 DRIVE  
 AKM MOTOR EURO STYLE  
 FEEDBACK RESOLVER CABLE