








7C Raymond Avenue
Salem, NH 03079

Speed-Thrust Performance Curves for IDC Actuators with new T-series and BK-series Motor Options





(Note: Use “P22” curves in the IDC 2000 catalog for “T22” performance)








EC2-BK23-xx-04A








EC2-BK23-xx-05B







EC2-BK23-xx-16B








EC2-T31-xx-04B









EC2-T31-xx-05B








EC2-T31-xx-16B








EC3-BK23-xx-04A








EC3-BK23-xx-05B







EC3-BK23-xx-10B






EC3-BK23-xx-16B







EC3-BK32-xx-04A







EC3-BK32-xx-05B








EC3-BK32-xx-10B








EC3-BK32-xx-16B








EC4-BK32-xx-10B








EC4-BK32-xx-25B








EC5-BK32-xx-10B








EC5-BK32-xx-32B








EC5-BK42-xx-10B








EC5-BK42-xx-32B






EC5-T41-xx-10B







EC5-T41-xx-32B







N2-BK23-xx-2B







N2-BK23-xx-5A





N2-BK23-xx-5B






N2-BK23-xx-8A






N2-T31-xx-2B




N2-T31-xx-5A




N2-T31-xx-5B





R2A-BK23-20T




R2A-BK23-xx-2B




R2A-BK23-xx-5A




R2A-BK23-xx-5B




R2A-T31-20T







R3-BK23-50T







R3-BK23-70T






R3-BK23-xx-2B




R3-BK23-xx-5A




R3-BK23-xx-5B




R3-BK32-20T




R3-BK23-50T




R3-BK32-70T




R3-T31-50T






R3-T31-70T






R3-T31-xx-2A







R3-T31-xx-2B




R3-T31-xx-5A




R3-T31-xx-5B




R4-BK32-30T








R4-BK32-50T







R4-BK32-100T




R4-BK32-xx-1B




R4-BK32-xx-4B




R4-BK42-20T








R4-BK42-50T






R4-BK42-100T




R4-BK42-xx-1B




R4-BK42-xx-4B








R4-T32-50T







R4-T32-100T




R4-T32-xx-1B




R4-T32-xx-4B




R4-T41-20T








R4-T41-50T



R4-T41-100T



R4-T41-xx-1B



R4-T41-xx-4B

