

Hookup Table for cable model CF-SS-CHAE-XX					
Motor Pin Name	Motor Plug Pin #	Wire Color	Gage	DB-25 Pin #	Drive Pin Name
A	1	BLUE	26	1	A
A\	2	BLUE/BLACK		2	/A
B	3	GREEN		4	B
B\	4	GREEN/BLACK		5	/B
Z	5	YELLOW		15	INDEX
Z\	6	YELLOW/BLACK		16	/INDEX
Hab = S1	17	ORANGE		9	H1B
Hbc = S2	16	GRAY		10	H2B
Hca = S3	15	ORANGE/BLACK		11	H3B
THERMOSTAT	8	VIOLET		13	Thermostat High
	9	VIOLET/WHITE		25	Thermostat Low
+5V	10	RED	18	19	E5V Supply
Common	7	BLACK		7	E5V Return
	N/C	TO PIN 18, DB-25	26	22	H1A
				23	H2A
				24	H3A
	Housing	TO PINS 22,23,24		18	E5V Supply
		THERM SHIELD		Housing	Chassis
		OVERALL SHIELD			
OPTIONAL	10	RED/WHITE	18	20	E5V Supply
	7	BLACK/WHITE		8	E5V Return