

PRHZ2.E136406 - Servo and Stepper Motors - Component

Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

Servo and Stepper Motors - Component

KOLLMORGEN CORP

201 W ROCK RD
RADFORD, VA 24141-4026 United States

E136406

Marking: Company name or tradename "API Controls", "Danaher Motion", "Pacific Scientific", "Superior", or trademark

   , model designation, and the Recognized Component Mark 

Note: For additional marking information, refer to the [Guide Information Page](#).

Model(s): B-102-A, B-102-B, B-104-A, B-104-B, B-104-C, B-106-A, B-106-B, B-106-C, B-412-W (a), B-414-V (a), B-414-W (a), B-612-A (a), M21, M22, M-413-W (a), M-615-A (a), P21, P22, P2H

Model(s): B or BE, followed by -20, -24, -40, -60 or -80, followed by 2, 4, 6, 7, 8 or 14, may be followed by additional numbers or letters.

Model(s): BH or MH, followed by 12, 22, 42, 62, or 82, followed by 2, 3, 4, 5, 6, 7, 8, or 9, may be followed by additional numbers or letters.

Model(s): BH, followed by 624, 626, 824, 826 or 828, may be followed by additional numbers or letters.

Model(s): C or CH, followed by 04, 05 or 06, followed by 1 to 4, followed by A or B or R or S or T or Custom, followed by additional suffixes.

Model(s): C or CH, followed by 09 or 13, followed by 1, 2, 3 or 9, followed by A, B or R or S or T or Custom, followed by additional suffixes.

Model(s): D or DH, followed by 06, 08, 10 or 14, followed by 1, 2, 3 or 9, followed by A, B, M or N, followed by additional numbers and letters.

Model(s): EK followed by M, followed by 2 to 7, followed by 1 to 5, followed by A to Z or 1 to 9, followed by A to Z or 1 to 9, followed by A to Z or 1 to 9, followed by A to Z or 1 to 9, followed by two numbers or letters, A to Z or 0 to 9, followed by two numbers or letters, A to Z or 0 to 9.

Model(s): F or FH followed by 4305, 4309, 4318, 5708, 5716, 5732, 7913, 7925, 7950, 10225, 10250 or 102100, followed by A or B, followed by additional suffixes

Model(s): M or ME, followed by -10, -20, -40, -41, -60, -61, -80, followed by 3, 5, 7 or 9, may be followed by additional numbers or letters.

Model(s): V or VH, followed by -31, followed by -41, -44 or -48, followed by AE, CE, DE, GE or VE.

Model(s): V, followed by -20, followed by -31 or -34, followed by A, B, C, D or HN.

Model(s): V, followed by -26, followed by -01 or -04, followed by A, AA, B, C, D, E, W, HE, JE, VE or VN.

Model(s): VLM, may be followed by 2 or 3, followed by 1, 2 or 3, followed by alpha numeric characters.

(a) - May be followed by -A9, followed by -B2, followed by -054.

Last Updated on 2022-09-26

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2023 UL LLC."