



mit / with UL-Recognition us

| | | | | | | |
|---|-----------------|---|-----------------------------|----------------|----------|------------|
| Type: | FZECU600x65-15 | Schutzart: Degree of protection: | IP 20 | | | |
| Widerstandswert: resistance value: | 15 Ohm | Klemme: terminal: | G10/2 | | | |
| Typleistung: continuous dissipation: | 1000 Watt | Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.: | BAR(U) 1000-15 DE-201440 | | | |
| Allgemein- toleranz ISO 2768 - m | | Maßstab M 1:4 | SolidWorks A4 | | | |
| Datum | | Werkstoff | | | | |
| (h) | | Rohrfestwiderstand / Tubular fixed resistor Type FZECU600x65-15 | | | | |
| (g) | Bearb. 18.02.10 | | | Name Pierri | | |
| (f) | Gepr. | | | | | |
| (e) | Norm. | | | | | |
| (d) | | | | | | |
| (c) | | 11D 42540 | | | | |
| (b) | | Blatt 1 | | | | |
| (a) | | 1 Bl. | | | | |
| Index | Änderung | Datum | Name | Urspr. | Ers. für | Ers. durch |