



mit / with UL-Recognition 

Type:	FZECU600x65-23	Schutzart: Degree of protection:	IP 20				
Widerstandswert: resistance value:	23 Ohm	Klemme: terminal:	G10/2				
Typleistung: continuous dissipation:	1000 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 1000-23 DE-200614				
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:4	SolidWorks A4				
Datum		Werkstoff					
(h)		Rohrfestwiderstand / Tubular fixed resistor Type FZECU600x65-23					
(g)	Bearb. 18.02.10			Pierri			
(f)	Gepr.						
(e)	Norm.						
(d)		11D 37664					
(c)							
(b)							
(a)		Blatt 1					
Index	Änderung	Datum	Name	Urspr.	Ers. für	Ers. durch	1 Bl.