



mit / with UL-Recognition

Type:	FZECU600x65-66	Schutzart: Degree of protection:	IP 20			
Widerstandswert: resistance value:	66 Ohm	Klemme: terminal:	G10/2			
Typeleistung: continuous dissipation:	1000 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 1000-66 DE-107163			
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:5	SolidWorks A4			
Datum		Werkstoff				
(h)		Rohrfestwiderstand / Tubular fixed resistor Type FZECU600x65-66				
(g)	Bearb. 18.02.10			Name Pierri		
(f)	Gepr.					
(e)	Norm.					
(d)						
(c)		11D 25187				
(b)				Blatt 1		
(a)				1 Bl.		
Index	Änderung	Datum	Name	Urspr.	Ers. für	Ers. durch