



mit / with UL-Recognition

Type:	FZECU600x65-91	Schutzart: Degree of protection:	IP 20
Widerstandswert: resistance value:	91 Ohm	Klemme: terminal:	G10/2
Typeleistung: continuous dissipation:	1000 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 1000-91 DE-107166

		Allgemein-toleranz ISO 2768 - m		Maßstab M 1:5		SolidWorks A4		
				Werkstoff		Rohrfestwiderstand / Tubular fixed resistor Type FZECU600x65-91 11D 25190		
(h)			Datum	Name				
(g)		Bearb.	25.10.10	Pe				
(f)		Gepr.						
(e)		Norm.						
(d)								
(c)								
(b)								
(a)								
Index	Änderung	Datum	Name	Urspr.	Ers. für	Ers. durch	Blatt 1 1 Bl.	