



mit / with UL-Recognition 

Type:	FZECU200x65-33	Schutzart: Degree of protection:	IP 20
Widerstandswert: resistance value:	33 Ohm	Klemme: terminal:	G10/2
Typeleistung: continuous dissipation:	250 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 250-33 DE-106254
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:3	SolidWorks A4
Werkstoff		Rohrfestwiderstand / Tubular fixed resistor Type FZECU200x65-33	
(h)		Datum	Name
(g)		Bearb. 15.02.10	Pierrri
(f)		Gepr.	
(e)		Norm.	
(d)			
(c)			
(b)			
(a)			
Index	Änderung	Datum	Name
		Urspr.	
11D 24150		Ers. für	Ers. durch
			Blatt 1
			1 Bl.