



mit / with UL-Recognition  us

Type:	FZECU200x65-66	Schutzart: Degree of protection:	IP 20
Widerstandswert: resistance value:	66 Ohm	Klemme: terminal:	G10/2
Typeleistung: continuous dissipation:	300 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 300-66 DE-107161
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:3	SolidWorks A4
Werkstoff		Rohrfestwiderstand / Tubular fixed resistor Type FZECU200x65-66	
(h)		Datum	Name
(g)		Bearb. 25.10.10	Pe
(f)		Gepr.	
(e)		Norm.	
(d)			
(c)			
(b)			
(a)			
Index	Änderung	Datum	Name
		Urspr.	
11D 25185		Ers. für	Ers. durch
			Blatt 1 1 Bl.