



mit / with UL-Recognition 

Type:	FZECU400x65-15	Schutzart: Degree of protection:	IP 20			
Widerstandswert: resistance value:	15 Ohm	Klemme: terminal:	G10/2			
Typleistung: continuous dissipation:	500 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 500-15 DE-201439			
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:4	SolidWorks A4			
Datum		Werkstoff				
(h)		Rohrfestwiderstand / Tubular fixed resistor Type FZECU400x65-15				
(g)	Bearb. 18.02.10			Pierri		
(f)	Gepr.					
(e)	Norm.					
(d)		11D 42539				
(c)				Blatt		
(b)				1		
(a)		1 Bl.				
Index	Änderung	Datum	Name	Urspr.	Ers. für	Ers. durch