



mit / with UL-Recognition 

Type:	FZECU400x65-23	Schutzart: Degree of protection:	IP 20	
Widerstandswert: resistance value:	23 Ohm	Klemme: terminal:	G10/2	
Typleistung: continuous dissipation:	600 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAR(U) 600-23 DE-200613	
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:4	SolidWorks A4	
Datum		Werkstoff		
(h)		Rohrfestwiderstand / Tubular fixed resistor Type FZECU400x65-23		
(g)	Bearb. 18.02.10			Pierri
(f)	Gepr.			
(e)	Norm.			
(d)				
(c)		11D 38334		
(b)		Blatt 1		
(a)		1 Bl.		
Index	Änderung	Datum	Name	
		Urspr.	Ers. für	
			Ers. durch	