



mit / with UL-Recognition  us

<b>Type:</b>	FGFKU3150402-10	<b>Schutzart:</b> Degree of protection:	IP 20
<b>Widerstandswert:</b> resistance value:	10 Ohm	<b>Klemme:</b> terminal:	G10/2
<b>Typeleistung:</b> continuous dissipation:	2000 Watt	<b>Kunden Art. Bez. / Art.Nr.:</b> Customer art. ident. / art. no.:	BAS(U) 2000-10 DE-103874
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:6	SolidWorks A4
Werkstoff		Stahlgitterfestwiderstand/ Steel- grid fixed resistor Type FGFKU3150402-10	
(h)		Datum	Name
(g)		Bearb. 25.10.10	Pe
(f)		Gepr.	
(e)		Norm.	
(d)			
(c)			
(b)			
(a)			
16D 18832		Blatt 1	
1 Bl.			
Index	Änderung	Datum	Name Urspr.
Ers. für		Ers. durch	