



mit / with UL-Recognition 

| | | | |
|---|-----------------|--|-----------------------------|
| Type: | FGFKU3100602-15 | Schutzart: Degree of protection: | IP 20 |
| Widerstandswert: resistance value: | 15 Ohm | Klemme: terminal: | G10/2 |
| Typleistung: continuous dissipation: | 3000 Watt | Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.: | BAS(U) 3000-15 DE-103872 |
| Allgemein- toleranz ISO 2768 - m | | Maßstab M 1:6 | SolidWorks A4 |
| Werkstoff | | Stahlgitterfestwiderstand/ Steel- grid fixed resistor Type FGFKU3100602-15 | |
| (h) | | Datum | Name |
| (g) | | Bearb. 01.03.10 | Pierri |
| (f) | | Gepr. | |
| (e) | | Norm. | |
| (d) | | | |
| (c) | | | |
| (b) | | | |
| (a) | | | |
| Index | Änderung | Datum | Name |
| | | | Urspr. |
| 16D 18825 | | Ers. für | Ers. durch |
| | | | Blatt 1 1 Bl. |