



mit / with UL-Recognition 

Type:	FGFKU3100602-33.6	Schutzart: Degree of protection:	IP 20
Widerstandswert: resistance value:	33.6 Ohm	Klemme: terminal:	G10/2
Typeleistung: continuous dissipation:	3000 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAS(U) 3000-33 DE-201407
Allgemein-toleranz ISO 2768 - m		Maßstab M 1:6	SolidWorks A4
Werkstoff		Stahlgitterfestwiderstand/ Steel- grid fixed resistor Type FGFKU3100602-33.6	
(h)		Datum	Name
(g)		Bearb. 18.02.10	Pierri
(f)		Gepr.	
(e)		Norm.	
(d)			
(c)			
(b)			
(a)			
Index	Änderung	Datum	Name
		Urspr.	
16D 42538		Ers. für	Ers. durch
			Blatt 1 1 Bl.