



mit / with UL-Recognition 

Type:	FGFKU3100802-23	Schutzart: Degree of protection:	IP 20			
Widerstandswert: resistance value:	23 Ohm	Klemme: terminal:	G10/2			
Typeleistung: continuous dissipation:	4000 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAS(U) 4000-23 DE-200617			
Allgemein- toleranz ISO 2768 - m		Maßstab M 1:6	SolidWorks A4			
Datum		Werkstoff				
(h)		Stahlgitterfestwiderstand/ Steel- grid fixed resistor Type FGFKU3100802-23				
(g)	Bearb. 18.02.10			Name Pierri		
(f)	Gepr.					
(e)	Norm.					
(d)						
(c)		16D 38339				
(b)		Blatt 1				
(a)		1 Bl.				
Index	Änderung	Datum	Name	Urspr.	Ers. für	Ers. durch