



mit / with UL-Recognition  us

Type:	FGFKU3100602-10	Schutzart: Degree of protection:	IP 20
Widerstandswert: resistance value:	10 Ohm	Klemme: terminal:	G10/2
Typeistung: continuous dissipation:	3000 Watt	Kunden Art. Bez. / Art.Nr.: Customer art. ident. / art. no.:	BAS(U) 3000-10 DE-103875

		Allgemein-toleranz ISO 2768 - m		Maßstab M 1:6		SolidWorks A4	
				Werkstoff			
(h)			Datum	Name		Stahlgitterfestwiderstand/ Steel- grid fixed resistor Type FGFKU3100602-10	
(g)		Bearb.	25.10.10	Pe			
(f)		Gepr.					
(e)		Norm.					
(d)							
(c)							
(b)							
(a)							
Index	Änderung	Datum	Name	Urspr.	Ers. für	Ers. durch	Blatt 1 1 Bl.