


FACE VIEW



N/C DENOTES NO CONNECTION

VP-508DFAN-xx-x(x)

- 1) Cable Specifications:
 - Jacket Material: TPE
 - Outside Diameter: $\phi 12.90\text{mm} \pm 0.20\text{mm}$
 - Bend Radius (min): 129mm
 - Static Flex Rating: Not Rated
 - Dynamic Flex Rating: Not Rated
 - Temperature Rating: 105°C
 - Voltage Rating: 600V
 - AWM Style: UL20328

- 2) Assembly Weight - SEE TABLE
- 3) This assembly is RoHS COMPLIANT

VP-508DFAN-01-0	0.328KG
VP-508DFAN-03-0	0.983KG
VP-508DFAN-06-0	1.966KG
VP-508DFAN-09-0	2.949KG
VP-508DFAN-12-0	3.932KG
ASSEMBLY WEIGHT	

DANAHER MOTION
 AKD DRIVE
 AKM MOTOR EURO STYLE
 24 AMP POWER CABLE w/BRAKE