#### **KOLLMORGEN**

### Value Delivered.

# Kollmorgen's new PMX<sup>™</sup> stepper motor line delivers breadth and design flexibility at competitive lead times.

Kollmorgen is excited to continue its winning heritage in hybrid stepper motors by introducing the PMX family. Leveraging the best practices from customer preferred products in the POWERMAX and POWERPAC families, the PMX lines will deliver breadth and design flexibility at a very competitive lead time. Look no further for that hybrid stepper motor family with local support that gives you the flexibility you need to succeed.

- Large range of sizes and options supports numerous performance and size requirements to meet your application needs from a single motion source.
- **Lower Unit Cost.** PMX motors are priced competitively in today's current stepper market and are the lowest of all Kollmorgen stepper products.
- Quality construction translates to reliability in the field and a long service life.
- Localized Support gives you the delivery terms and immediate technical support you need, meaning to guicker time to market and less downtime.
- Flexible Manufacturing enables Kollmorgen to immediately evaluate modifications and co-engineered solutions for rapid prototyping.



PMX motors allow Kollmorgen customers to fulfil their automation needs at an affordable cost, enabling higher throughput in a wide variety of equipment. In addition, leveraging Kollmorgen's technical expertise and flexible engineering, the PMX is ready for seamless special and co-engineering options, allowing for swifter and easier integration into both new and existing applications.

## Standard



#### **Features**

- Six frame sizes (08, 11, 14, 17, 23, 34) each with several stack length and winding options available
- Multiple front and rear shaft configurations
- CE, RoHS, and REACH compliant
- Use with Kollmorgen Stepper drives for system solution

#### **Benefits**

- Increased design flexibility
- Reliability over long service life
- Low unit cost without sacrificing performance and support

# **Added Modifications**



#### **Features**

- Shaft modifications
- Special windings
- Special connectors and cabling
- Encoders
- Gearboxes

#### **Benefits**

- Swifter integration and prototyping
- Reduction of on-site labor requirements
- Modifications can match and replace pre-existing motors at a lower cost

# Chemical Analyzers PMX Stepper Motors

Tabletop Equipment

3-D Printers

Metering Pumps

## **Customized Solutions**



#### **Features**

 Complete motor subassemblies and system design available through full co-engineering with Kollmorgen

#### **Benefits**

- Design optimization
- Assembly is "drop-in" ready for plug & play machine integration
- Reduced machine SKU count
- Reduction in machine assembly time

# PMX<sup>™</sup> Stepper Motor Overview

# Standard Options o available option

		Product Family	NEMA	Step	Stacks	Holding	g <b>Torque (o</b> z 1200	<b>z-in)</b> 2000	CE Mark	RoHS	Integral Connectoin	Leadwire		6-Lead Unipolar IP Sealing		Hat had		Rear Shaft
Economy, Push		PMX08	08	1.8°	2	4.0			•	•		•	•	30	0	•		•
		PMX11	11	1.8°	3	16.8			•	•		•	•	30	0	•		•
		PMX14	14	1.8°	3	26.4			•	•		•	•	30	0	•		•
		PMX17	17	0.9° 1.8°	5	107.0			•	•	•	•	•	o 30	0	•		•
		PMX23	23	0.9° 1.8°	4	378.0			•	•	•	•	•	° 30, 65¹	0	•		•
		PMX34	34	1.8°	4		173	39	•	•		•	•	30, 65 <sup>1</sup>	0	•	0	•

## **PMX<sup>™</sup> Dimensional Overview**

NEMA			"B" MAX	Ø " <b>C</b> "			
Frame	Stacks						Shaft Diameter
≣e	1	2	3	4	5	Size	Shall Diameter
08	<b>30</b> [1.18]	<b>42</b> [1.65]		-	-	20.2 [0.80]	4 -0.013 [ 0.16 -0.0005 ]
11	<b>32</b> [1.26]	<b>45</b> [1.77]	<b>51</b> [2.01]		-	28.2 [1.11]	5-0.013 [0.20-0.0005]
14	<b>26</b> [1.02]	<b>28</b> [1.10]	<b>36</b> [1.42]	-	-	35.2 [1.39]	$5_{-0.013} \ [0.20_{-0.0005}]$
17	<b>26</b> [1.02]	<b>33.5</b> [1.32]	<b>39.5</b> [1.56]	<b>47.5</b> [1.87]	<b>60</b> [2.36]	42.3 [1.67]	5 <sub>-0.013</sub> [ 0.20 <sub>-0.0005</sub> ]
23	<b>41</b> [1.61]	<b>56</b> [2.20]	<b>76</b> [2.99]	<b>85</b> [3.35]		56.4 [2.22]	6.35 _0.013 [0.25 _0.0005]
34	<b>65</b> [2.56]	<b>80</b> [3.15]	<b>118</b> [4.65]	<b>156</b> [6.14]		85.85 [3.83]	12.7 _0.012 [0.50_0.0005]

Dimensions in mm [inches]





						_				_	•										
		Ava	ilat	ole N	loto	r	Available Options					A	Available Options								
1 Motor Series	PMX						Motor Series			PMX					Motor Series			PI	ИΧ		
2 NEMA Frame	08	11	14	17	23	34	<b>NEMA Frame</b>	Sizes	08	11	14	17	23	34	NEMA Frame Sizes	08	11	14	17	23	34
3 Rotor Stack Lengt	h						6 Connection	/Option							8 Rear Shaft Option						
1 = 1 stack	•	•	•	•	•	•	B = 4 lead Bipo	olar	•	•	•	•	•	•	0 = No rear shaft	•	•	•	•	•	•
2 = 2 stacks	•	•	•	•	•	•	U = 6 lead Unip	polar				•	•		R = Rear shaft	•	•	•	•	•	•
3 = 3 stacks		•		•	•	•	X = Integrated	Connector				•	•		9 Sealing Option						
4 = 4 stacks				•	•	•	<b>7</b> Front Shaft	Option							00 = IP30	•	•	•	•	•	•
5 = 5 stacks				•			N = Smooth fro		•	•	•	•	•	•	01 = IP65 sealing					•	•
4 Motor Winding							F = Flat front s	haft	•	•	•	•	•	•							
Bipolar (A through D)	•	•	•	•	•	•	K = Open keyw	<i>v</i> ay						•							
Unipolar (G through J)				•	•																
5 Step Angle																					
1 = 1.8°	•	•	•	•	•	•															
9 = 0.9°				•	•																

KOLLMORGEN

www.kollmorgen.com